





Mini circuit breaker, QO, 20A, 3 pole, 120/240VAC, 22kA, bolt on

QOB320VH

Product availability: Stock - Normally stocked in distribution facility

Price*: 475.20 USD

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number Of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	22 kA 120/240 V AC
	22 kA 240 V AC
	22 kA 120 V AC
Number Of Panel Spaces	3
Wire Size	AWG 14AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.80 lb(US) (0.363 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
Gtin	785901371960
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.6 cm)
Package 1 Width	3.03 in (7.7 cm)
Package 1 Length	3.31 in (8.4 cm)
Package 1 Weight	13.12 oz (372 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	3.50 in (8.9 cm)
Package 2 Width	3.62 in (9.2 cm)
Package 2 Length	6.81 in (17.3 cm)
Package 2 Weight	2.53 lb(US) (1.148 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	36
Package 3 Height	3.70 in (9.4 cm)
Package 3 Width	14.41 in (36.6 cm)
Package 3 Length	21.34 in (54.2 cm)
Package 3 Weight	31.01 lb(US) (14.066 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations