





Enclosed circuit breaker, QO, 2 pole, 1 phase, 50A, NEMA3R, ground fault protection, nonmetalic, spa

QOE250GFINM

Product availability: Stock - Normally stocked in distribution facility

Price\*: 528.00 USD

#### Main

Product Type	Enclosed circuit breaker
Range Of Product	QO
Load Center Type	Main breaker

### Complementary

Current Rating	50 A	
Interrupt Rating	10 kA	
Number Of Spaces	2	
Number Of Phases	1 phase	
Enclosure Rating	NEMA 3R outdoor	
Breaker Compatibility	Circuit breaker QO-GFI 2P	
Product Certifications	oduct Certifications UL Listed	
Wiring Configuration	ng Configuration 3-wire	
Electrical Connection	onnection Lugs	
Surface Finish	Baked enamel Gray	
Voltage Rating	120/240 V AC	
Box Number	1NM	
Ground Bar	Grounding bar (factory installed)	
Enclosure Material	sure Material Non-metallic	
Enclosure Type	re Type Enclosure	
Height	9.17 in (233 mm)	
Width	6.54 in (166 mm)	
Depth	3.90 in (99 mm)	

## Ordering and shipping details

Category	US1DE3A00167
Discount Schedule	DE3A
Gtin	785901389507
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	6.80 in (17.272 cm)
Package 1 Length	9.50 in (24.13 cm)
Package 1 Weight	2.40 lb(US) (1.089 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	10.60 in (26.924 cm)
Package 2 Width	13.20 in (33.528 cm)
Package 2 Length	20.30 in (51.562 cm)
Package 2 Weight	24.90 lb(US) (11.294 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	240
Package 3 Height	46.50 in (118.11 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	645.00 lb(US) (292.567 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov