

# Product data sheet

Specifications



Load center interior, QO, mounting base, 3 phase, 30 spaces, 200A main lugs, OEM

QON330L200

Product availability: Stock - Normally stocked in distribution facility

Price\*: 477.00 USD

## Main

Product Type	Mounting base
Marketing Trade Name	QO
Load Center Type	Main lugs
Rated Current	200 A
Number Of Spaces	30
Max Short Circuit Current Rating	10 kA
Number Of Phases	3 phase 3 wires
Voltage Rating	120/240 V AC

## Complementary

Wire Size	AWG 4...300 kcmil aluminium/copper
Product Certifications	CSA UL
Height	14.76 in (375 mm)
Width	7.95 in (202 mm)
Depth	3.03 in (77 mm)
Net Weight	3.00 lb(US) (1.361 kg)

## Ordering and shipping details

Category	US1DE3A00909
Discount Schedule	DE3A
Gtin	785901868279
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.10 in (10.414 cm)
Package 1 Width	13.00 in (33.02 cm)
Package 1 Length	21.00 in (53.34 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	3.78 lb(US) (1.715 kg)
------------------	------------------------

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>