





Mini circuit breaker, QOU, 10A, 1 pole, 120/240VAC, 10kA

QOU110

Product availability: Stock - Normally stocked in distribution facility

Price*: 40.20 USD

Main

Product Or Component Type	Miniature circuit-breaker
Range Of Product	QOU
Circuit Breaker Type	Standard
Circuit Breaker Application	HACR rated

Complementary

Line Rated Current	10 A
Electrical Connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] Rated Operational Voltage	120/240 V AC 120 V AC 48 V DC
Mounting Mode	Unit mount
Awg Gauge	AWG 14AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	0.75 in (19.05 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

Environment

Product Certifications	IEC CSA
	UL Listed

Ordering and shipping details

Category	US10DE200900
Discount Schedule	0DE2
Gtin	785901205678
Returnability	Yes
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	6.40 oz (181.437 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	66
Package 2 Height	3.30 in (8.382 cm)
Package 2 Width	14.00 in (35.56 cm)
Package 2 Length	20.90 in (53.086 cm)
Package 2 Weight	24.75 lb(US) (11.226 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	2772
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	1014.00 lb(US) (459.942 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration