





# Mini switch, QOU, non-automatic, 60A, 2 pole, 240 VAC, 10kA

QOU200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 93.96 USD

#### Main

Product Or Component Type	Switch
Range Of Product	QOU
Circuit Breaker Application	HACR rated

#### Complementary

•	2
Line Rated Current	60 A
Electrical Connection	Slotted box lugs, line side Slotted box lugs, load side
Mounting Mode	Unit mount
Awg Gauge	AWG 12AWG 2/0 aluminium/copper
Height	4.05 in (102.87 mm)
Width	1.5 in (38.10 mm)
Depth	2.95 in (74.93 mm)
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

#### **Environment**

Product Certifications	UL Listed
	CSA

## Ordering and shipping details

	11 0	
Category	US10DE200900	
Discount Schedule	0DE2	
Gtin	785901371717	
Returnability	No	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	4.90 in (12.446 cm)
Package 1 Weight	11.20 oz (317.515 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

<b>Ø</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations