





# Mini circuit breaker, QOU, 25A, 3 pole, 240 VAC, 10kA

QOU325

Product availability: Stock - Normally stocked in distribution

Price\*: 307.80 USD

### Main

| Product Or Component Type   | Miniature circuit-breaker |
|-----------------------------|---------------------------|
| Range Of Product            | QOU                       |
| Circuit Breaker Type        | Standard                  |
| Circuit Breaker Application | HACR rated                |

### Complementary

| Line Rated Current             | 25 A   |
|--------------------------------|--|
| Electrical Connection          | Slotted box lugs, line side<br>Slotted box lugs, load side |
| [Ue] Rated Operational Voltage | 120/240 V AC<br>240 V AC<br>120 V AC<br>48 V DC            |
| Mounting Mode                  | Unit mount   |
| Awg Gauge                      | AWG 14AWG 2 aluminium/copper                               |
| Height                         | 4.05 in (102.87 mm)  |
| Width                          | 2.25 in (57.15 mm)   |
| Depth                          | 2.95 in (74.93 mm)   |
| Tightening Torque              | 45 lbf.in (5.08 N.m) (AWG 14AWG 2)                         |

#### **Environment**

| Product Certifications | CSA       |
|------------------------|-----------|
|                        | UL Listed |
|                        | IEC       |

## Ordering and shipping details

| Category          | US10DE200900 |
|-------------------|--------------|
| Discount Schedule | 0DE2         |
| Gtin              | 785901489177 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

## **Packing Units**

| Unit Type Of Package 1       | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Height             | 2.60 in (6.604 cm)          |
|------------------------------|-----------------------------|
| Package 1 Width              | 3.50 in (8.89 cm)           |
| Package 1 Length             | 4.80 in (12.192 cm)         |
| Package 1 Weight             | 18.08 oz (512.559 g)        |
| Unit Type Of Package 2       | PAL                         |
| Number Of Units In Package 2 | 840                         |
| Package 2 Height             | 40.00 in (101.6 cm)         |
| Package 2 Width              | 40.00 in (101.6 cm)         |
| Package 2 Length             | 48.00 in (121.92 cm)        |
| Package 2 Weight             | 1085.00 lb(US) (492.147 kg) |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

| <b>Ø</b> | Toxic Heavy Metal Free     |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Mercury Free               |     |
| <b>②</b> | Rohs Exemption Information | Yes |
| <b>⊘</b> | Halogen Free Product       |     |

## **Certifications & Standards**

| Reach Regulation      | REACh Declaration  |
|-----------------------|--|
| Eu Rohs Directive     | Compliant with Exemptions  |
| China Rohs Regulation | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information. |
| Circularity Profile   | No need of specific recycling operations   |