





Mini circuit breaker, QO, 32A, 1 pole, 240/415VAC, 3kA, plug in

QOXD132

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 30.60 USD

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	32 A	
Voltage Rating	240/415 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	

Complementary

Interrupt Rating	Icu 3 kA 240/415 V AC IEC 947-2	
Tightening Torque	44.25 lbf.in (5 N.m) 0.020.04 in² (1025 mm²) (AWG 8AWG 2)	
Net Weight	0.30 lb(US) (0.136 kg)	

Environment

Ambient Rating 104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00920
Discount Schedule	DE2A
Gtin	785901708896
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.80 in (2.032 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	4.80 oz (136.078 g)

Contractual warranty

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Circularity Profile	No need of specific recycling operations