





Meter Mains

Meter mains, Homeline, CSED, ringless socket, 125A, surface mount, maximum 8 spaces, 16 circuits, horn bypass

RC816F125CH

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,227.00 USD

#### Main

Product Or Component Type

Range Of Product	Homeline
-	
Complementary	
Line Rated Current	125 A
Short-Circuit Current	22 kA
Network Number Of Phases	1
Meter Socket Type	Ringless
Mounting	Surface
Number Of Spaces	8
Number Of Circuits	16
Number Of Tandem Breakers	8
Hub Type	A
Electrical Connection	Lugs, line side Feed-thru lugs, service ground
Wire Size	AWG 6350 kcmil aluminium/copper)line side AWG 12AWG 2/0 aluminium/copper)service ground
Tightening Torque	Main lugs 250 lb.in, AWG 6350 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14AWG 2/0, copper Service ground 50 lb.in, AWG 12AWG 2/0, aluminium Branch lugs 35 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14AWG 10, copper Branch lugs 20 lb.in, AWG 12AWG 10, aluminium Cover 10 lb.in
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	125 A
Branch Breaker Rating	100 A
Service Feed Location	OH UG
Bypass Type	Horn bypass
Height	35.13 in (892.30 mm)
Width	14.37 in (365.00 mm)
Depth	5.07 in (128.78 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Bus Rating 200.0 A

#### **Environment**

Product Certifications UL E-6294

# Ordering and shipping details

Category	US1DE3A00048
Discount Schedule	DE3A
Gtin	785901401834
Returnability	Yes
Country Of Origin	IIS

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.00 in (15.24 cm)
Package 1 Width	15.00 in (38.1 cm)
Package 1 Length	36.30 in (92.202 cm)
Package 1 Weight	42.11 lb(US) (19.101 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	21
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	912.00 lb(US) (413.676 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov