

# Product data sheet

Specifications

SQUARE D

## WIREWAY 12 X 12 RAIN TIGHT TROUGHS - 6 FT



RDB126

Product availability: Stock - Normally stocked in distribution facility

Price\*: 673.00 USD

### Main

|                    |  |
|--------------------|--|
| Busbar Description | Straight length  |
| Device Short Name  | RDB  |
| Enclosure Type     | Rainproof enclosure indoor/outdoor<br>Ice/sleet proof enclosure indoor/outdoor |
| Provided Equipment | removable cover sealable   |
| Range Of Product   | SQUARE-Duct  |

### Complementary

|                    |                               |
|--------------------|-------------------------------|
| Enclosure Material | 14 gauge steel                |
| Length             | 6 ft (1.83 m)                 |
| Surface Finish     | Gray polyester powder ANSI 49 |
| Trunking Dimension | 12 x 12 in                    |

### Environment

|                           |           |
|---------------------------|-----------|
| Nema Degree Of Protection | NEMA 3R   |
| Product Certifications    | UL Listed |

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10PE901422 |
| Discount Schedule | 0PE9         |
| Gtin              | 785901046769 |
| Returnability     | Yes          |
| Country Of Origin | US           |

### Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Height             | 12.80 in (32.5 cm)       |
| Package 1 Width              | 13.19 in (33.5 cm)       |
| Package 1 Length             | 71.89 in (182.6 cm)      |
| Package 1 Weight             | 91.00 lb(US) (41.277 kg) |

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

|                       |  |
|-----------------------|--|
| Eu Rohs Directive     | Not applicable, out of EU RoHS legal scope   |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information. |