

# Product data sheet

Specifications

SQUARE D

Green Premium™



Automatic switch, PowerPacT R, 2000A, 2 pole, 600VAC, 50kA, busbar, magnetic

RKF26000S20

## Main

Product Or Component Type	Automatic switch
Range Of Product	PowerPact R
Trip Unit Technology	Magnetic
Circuit Breaker Type	R-Frame

## Complementary

Line Rated Current	2000 A
[Ue] Rated Operational Voltage	600 V AC
Mounting Mode	Unit mount
Poles Description	2P
Short-Circuit Withstand	65 kA 240 V UL 489 65 kA 480 V UL 489 65 kA 600 V UL 489
Breaking Capacity Code	K
Electrical Connection	Busbar connection, line Busbar connection, load
Magnetic Tripping Current	57000 A
Height	16.24 in (412.50 mm)
Width	16.54 in (420.12 mm)
Depth	14.49 in (368.05 mm)
Tightening Torque	601.85 lbf.in (68 N.m) 0.08...0.62 in² (50...400 mm²) (AWG 1/0...750 kcmil) 601.85 lbf.in (68 N.m) 0.08...0.23 in² (50...150 mm²) (AWG 1/0...300 kcmil)

## Environment

Product Certifications	UL Listed CSA IEC
------------------------	-------------------------

## Ordering and shipping details

Category	01245-RG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Returnability	No
Country Of Origin	US

## Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.22 in (41.2 cm)
Package 1 Width	16.54 in (42.0 cm)
Package 1 Length	14.49 in (36.8 cm)
Package 1 Weight	74.00 lb(US) (33.566 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.





[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
	Pvc Free	
	Halogen Free Plastic Parts Product	

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>