





Circuit breaker, PowerPacT R, 1200A, 3 pole, 600VAC, 50kA, I-Line, Micrologic 6.0A, 100%

RLA36120CU44A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 43,434.00 USD

Main

| Wall | | |
|---------------------------|-------------------------|--|
| Range | PowerPact | |
| Product Name | PowerPact R | |
| Product Or Component Type | nt Type Circuit breaker | |
| Device Application | Distribution | |

Complementary

| oompromentary | |
|--|---|
| Line Rated Current | 1200 A |
| Number Of Poles | 3P |
| Control Type | Operating handle |
| Breaking Capacity Code | L |
| Breaking Capacity | AIR 125 kA 240 V AC 50/60 Hz UL 489 AIR 100 kA 480 V AC 50/60 Hz UL 489 AIR 50 kA 600 V AC 50/60 Hz UL 489 Icu 125 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 85 kA 380/415 V AC 50/60 Hz IEC 60947-2 |
| [Ue] Rated Operational Voltage | 600 V AC 50/60 Hz UL 489 |
| Network Frequency | 50/60 Hz |
| [Ics] Rated Service Breaking Capacity | 65 kA 240 V AC 50/60 Hz IEC 60947-2 45 kA 380/415 V AC 50/60 Hz IEC 60947-2 |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV IEC 60947-2 |
| Trip Unit Technology | Electronic, ammeter, MicroLogic 6.0 A, LSIG |
| Continuous Current Rating | 100 % |
| [Ui] Rated Insulation Voltage | 750 V IEC 60947-2 |
| Trip Unit Name | MicroLogic 6.0 A |
| Suitability For Isolation | Yes IEC 60947-2 |
| Utilisation Category | Category A |
| Awg Gauge | 4 x AWG 3/0600 kcmil aluminium/copper 4 x AWG 3/0500 kcmil copper |
| Local Signalling | Alarm 1 LED yellow)long-time pick up) 1 LED red)long-time pick up) Trip causes 1 LED red) 1 LED red)digital ammeter) Ground indicator 1 LED red) Phase-loading LED green)load balancing) |
| Mounting Mode | I-Line bracket) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Mounting Support | Bracket | |
|-----------------------------|---|--|
| Electrical Connection | I-Line connection, line Lugs, load | |
| Terminal Identifier | AL1200R53K | |
| Tightening Torque | 442.54 lbf.in (50 N.m) 0.150.47 in² (95300 mm²) (4 x AWG 3/0600 kcmil) | |
| Number Of Slots | 2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 voltage release MN or MX plug-in) | |
| Power Wire Stripping Length | 1.18 in (30 mm) | |
| Height | 16.24 in (412.50 mm) | |
| Width | 16.54 in (420.12 mm) | |
| Depth | 14.49 in (368.05 mm) | |
| Net Weight | 52 lb(US) (23.59 kg) | |
| Quantity Per Set | 1 | |
| Circuit Breaker Application | HACR rated | |

Environment

| Quality Labels | CE |
|---------------------------------------|--|
| Standards | UL CSA NEMA NMX J-266 IEC 60947-2 |
| Product Certifications | UL CSA NOM |
| Ip Degree Of Protection | IP40 |
| Pollution Degree | 3 IEC 60947-1 |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Ambient Air Temperature For Storage | -58185 °F (-5085 °C) |
| Operating Altitude | < 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating |

Ordering and shipping details

| Category | US10DE201240 0DE2 | |
|-------------------|----------------------|--|
| Discount Schedule | | |
| Gtin | 785901234111 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| _ | |
|------------------------------|--------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 13.39 in (34.0 cm) |
| Package 1 Width | 14.96 in (38.0 cm) |
| Package 1 Length | 13.78 in (35.0 cm) |

Package 1 Weight

52.00 lb(US) (23.587 kg)

Contractual warranty

Warranty

Apr 25, 2024

18 months

Sustainability Green Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free |
|----------|------------------------------------|
| ⊘ | Rohs Exemption Information Yes |
| ② | Pvc Free |
| ⊘ | Halogen Free Plastic Parts Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |