Product data sheet

Specifications





socket, Harmony Electromechanical Relays, for RXM2 RXM4 relays, screw connec to rs, separate contact

RXZE2S114M

Product availability: Stock - Normally stocked in distribution facility

Price*: 6.10 USD

Main

Range Of Product	Harmony Electromechanical Relays Harmony Timer Relays
Device Short Name	RXZ
Product Or Component Type	Socket
Product Compatibility	Plug-in relay RXM 4 C/O Plug-in relay REXL 4 C/O
Contacts Type And Composition	4 C/O
[Ith] Conventional Free Air Thermal Current	10 A

Complementary

j	
Shape Of Pin	Flat
[Ue] Rated Operational Voltage	< 250 V
Contact Terminal Arrangement	Separate
Connections - Terminals	Connector, 1 x 0.251 x 2.5 mm ² AWG 22AWG 14) flexible with cable end Connector, 2 x 0.252 x 1 mm ² AWG 22AWG 17) flexible with cable end Connector, 1 x 0.51 x 2.5 mm ² AWG 20AWG 14) solid without cable end Connector, 2 x 0.52 x 1.5 mm ² AWG 20AWG 16) solid without cable end
Tightening Torque	< 1 N.m M3
Fixing Mode	By screw (panel) Clip-on (35 mm symmetrical DIN rail)
[Uimp] Rated Impulse Withstand Voltage	4 kV
Overvoltage Category	III
Pollution Degree	3
Sale Per Indivisible Quantity	10
Width	1.06 in (27 mm)
Net Weight	0.15 lb(US) (0.07 kg)

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529	
Dielectric Strength	2500 V	
Standards	IEC 61984	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Certifications	CSA Lloyd's UL
Marking	CE
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)

Ordering and shipping details

Category	US10CP221128	
Discount Schedule	0CP2	
Gtin	3389119404280	
Returnability	Yes	
Country Of Origin	US	

Packing Units

0		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.05 in (2.679 cm)	
Package 1 Width	1.14 in (2.893 cm)	
Package 1 Length	3.24 in (8.219 cm)	
Package 1 Weight	2.19 oz (62.2 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	10	
Package 2 Height	2.60 in (6.6 cm)	
Package 2 Width	4.49 in (11.4 cm)	
Package 2 Length	5.39 in (13.7 cm)	
Package 2 Weight	23.44 oz (664.5 g)	
Unit Type Of Package 3	S03	
Number Of Units In Package 3	200	
Package 3 Height	11.81 in (30 cm)	
Package 3 Width	11.81 in (30 cm)	
Package 3 Length	15.75 in (40 cm)	
Package 3 Weight	29.10 lb(US) (13.2 kg)	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Dimensions



(1) Relays

(2) Protection module

(3) Maintaining clamp

(4) 2 elongated holes Ø 3.5 mm x 6.5 mm / Ø 0.13 in. x 0.25 in.

(5) 2 bus jumpers

Product data sheet

Connections and Schema

Wiring Diagram

