# **Product data sheet**

Specification





APC Smart-UPS, Line Interactive, 3kVA, Rackmount 2U, 120V, 6x NEMA 5-15R+2x NEMA 5-20R outlets, SmartSlot, AVR, LCD, With 12ft cord

SMT3000R2X145

#### **Overview**

Lead Time	Usually Ships within 3 Weeks
Main	
Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	2700 W
Rated Power In Va	2880 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA L5-30P
Output Connection Type	6 NEMA 5-15R 2 NEMA 5-20R
Number Of Rack Unit	2U
Cable Length	12 ft (3.66 m)
Number Of Cables	1
Battery Type	Lead-Acid battery
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting support rails Smart UPS signalling RS-232 cable USB cable

### **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical Recharge Time	3 h
Rbc Quantity	1
Battery Life	35 year(s)
Replacement Battery	RBC43 ☐
Battery Charge Power (Watts)	188 W rated

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

# **Physical**

Color	Black
Height	3.39 in (8.6 cm)
Width	18.90 in (48 cm)
Depth	26.89 in (68.3 cm)
Net Weight	97.62 lb(US) (44.28 kg)
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	Yes

# Input

Efficiency At Full Load	75154 V adjustable 82144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

# Output

Harmonic Distortion	Less than 5%
Maximum Configurable Power In Va	2880 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Wave Type	Sine wave
Output Frequency (Sync To Mains)	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product Certifications	CSA
Equipment Protection Policy	Lifetime: \$150000

## **Environmental**

Acoustic Level	55 dBA
Heat Dissipation	348 Btu/h
Operating Altitude	010000 ft
Ambient Air Temperature For Operation	32104 °F (040 °C)
Ambient Air Temperature For Storage	5113 °F (-1545 °C)
Storage Altitude	050000 ft (0.0015240.00 m)

Relative Humidity	095 %	
Storage Relative Humidity	0. 95 %	

# **Communications & Management**

Control Panel	Multi-function LCD status and control console
Free Slots	1
Control Panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## **Surge Protection and Filtering**

Surge Energy Rating 459

## Ordering and shipping details

Gtin	731304294092
Country Of Origin	PH

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	38.58 in (98 cm)
Package 1 Length	23.62 in (60 cm)
Package 1 Weight	113.98 lb(US) (51.7 kg)

## **Contractual warranty**

Warranty

3 years repair or replace (excluding battery) and 2 years for battery

# Sustainability Screen Premium

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

### Resource performance

**Energy Efficient Product** 



Take-Back Program Available

### Well-being performance

Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov