

# Product data sheet

Specifications



Starter, TeSys N, 90A, 50hp at 575VAC, 3 phase, NEMA size 3 at 120VAC

T36EN13G7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,185.00 USD

## Main

Product	Starter
Range Of Product	TeSys N
Current Rating	90 A
Certifications	UL Listed CSA
Control Circuit Type	Common control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	3
Control Circuit Voltage	120 V AC
Starter Type	Non reversing
Electrical Connection	Lugs ordered separately
Overload Type	Solid state Motor Logic class 10/20 30...90 A

## Ordering and shipping details

Category	US10CP121199
Discount Schedule	0CP1
Gtin	3606486289686
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.70 in (24.638 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	10.50 in (26.67 cm)
Package 1 Length	16.30 in (41.402 cm)
Package 1 Weight	15.10 lb(US) (6.849 kg)

# Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>