

Product data sheet

Specifications



SZ00 FVNR COMBO 12/3R CPT FLA 12

T40AA128V80NAP1

! Discontinued

Main

| | |
|---------------------------------|---|
| Product Or Component Type | Self-protected combination motor controller |
| Range Of Product | TeSys N Self-Protected Combination Motor Controller |
| Product Certifications | UL Listed CSA |
| Control Circuit | Control circuit transformer |
| Provided Equipment | 2 fuses (primary), 1 fuse (secondary) |
| Phase | 3 phase |
| [Ue] Rated Operational Voltage | 240 V AC |
| [Uc] Control Circuit Voltage | 120 V AC 50/60 Hz |
| Communication Port Protocol | Without |
| Nema Degree Of Protection | NEMA 12/3R |
| Enclosure Material | Painted sheet steel |
| Enclosure Type | Standard size |
| Enclosure Accessory Description | With external reset |
| Auxiliary Contact Composition | 1 NO + 1 NC |
| Nema Size | 00 |
| Maximum Horse Power Rating | 1.5 hp 230 V AC |
| Poles Description | 3P |
| Local Signalling | Red indicator on LED |
| Control Type | Push-button START-STOP) |
| Motor Starter Type | Non reversing |
| Electrical Connection | Screw-clamp terminals |
| Thermal Overload Type | Solid state advanced class 20 3...12 A |
| Disconnecter Device Type | Self-protected combination controller 9 A |

Ordering and shipping details

| | |
|-------------------|--|
| Category | 21219-ENCLOSED TESYS N COMB STR SIZE 1 |
| Discount Schedule | CP1 |
| Returnability | No |

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|--------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 24.62 lb(US) (11.167 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|