

Product data sheet

Specifications



SZ1 FVNR COMBO 1 SC ASI FLA 5

T40CG129BDJAP1S6

! Discontinued

Main

Product Or Component Type	Self-protected combination motor controller
Range Of Product	TeSys N Self-Protected Combination Motor Controller
Product Certifications	UL Listed CSA
Control Circuit	Separate control circuit
Provided Equipment	Current limiter
Phase	3 phase
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	24 V DC
Communication Port Protocol	AS-Interface
Nema Degree Of Protection	NEMA 1
Enclosure Material	Painted sheet steel
Enclosure Type	Standard size
Enclosure Accessory Description	With external reset
Auxiliary Contact Composition	1 NO + 1 NC
Nema Size	1
Maximum Horse Power Rating	10 hp 460 V AC 7.5 hp 230 V AC 7.5 hp 200 V AC 10 hp 575 V AC
Poles Description	3P
Local Signalling	Red indicator on LED
Control Type	Push-button START-STOP)
Motor Starter Type	Non reversing
Electrical Connection	Screw-clamp terminals
Thermal Overload Type	Solid state advanced class 20 1.25...5 A
Disconnecter Device Type	Self-protected combination controller 27 A

Ordering and shipping details

Category	21219-ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	24.62 lb(US) (11.167 kg)

Contractual warranty

Warranty	18 months
----------	-----------