Product data sheet

Specifications





ConneXium Unmanaged Switch - 8 ports for copper

TCSESU083FN0

! Discontinued on: Mar 15, 2022

Product availability: Non-Stock - Not normally stocked in distribution facility

① Discontinued

Main

Range Of Product	ConneXium
Product Or Component Type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication Port Protocol	Ethernet TCP/IP
Port Ethernet	10/100BASE-TX - 8 copper cable
Maximum Number Of Switches In Cascade	Unlimited

Complementary

Integrated Connection Type	Shielded RJ45 copper cable
Transmission Support Medium	Twisted shielded pairs cable CAT 5E copper cable
Maximum Cable Distance Between Devices	328.08 ft (100 m) copper cable
[Us] Rated Supply Voltage	1224 V
Supply Voltage Limits	9.632 V DC SELV
Power Consumption In W	4.1 W
Electrical Connection	Removable connector 3 ways power supply
Mounting Support	35 mm symmetrical DIN rail
Marking	CE UL RCM
Local Signalling	for power supply 1 LED (green) for data rate (ETH LINK) 1 LED per channel (yellow) for link status 1 LED per channel (green)
Ethernet Cabling System	TF switches
Width	1.38 in (35 mm)
Height	5.43 in (138 mm)
Depth	4.76 in (121 mm)
Net Weight	0.54 lb(US) (0.246 kg)

Environment

Ambient Air Temperature For Operation	32140 °F (060 °C)
Relative Humidity	095 % non-condensing
Ip Degree Of Protection	IP30

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 25, 2024 Life Is On Schneider 1

Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 61010 EN/IEC 61131
Product Certifications	CE UL RCM

Ordering and shipping details

_	• • •
Category	US1PC4118225
Discount Schedule	PC41
Gtin	00785901899020
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	6.38 in (16.2 cm)
Package 1 Length	9.53 in (24.2 cm)
Package 1 Weight	13.54 oz (384 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	, , , , , , , , , , , , , , , , , , , ,

Product data sheet

TCSESU083FN0

Connections and Schema

Power Wiring

