Product data sheet

Specifications





analogue output cartridge, Modicon M221, 2 analog voltage outputs, IO extension

TMC2AQ2V

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 89.00 USD

Main

Range Of Product	Modicon M221
Product Or Component Type	Analogue output cartridge
Product Compatibility	Modicon M221C

Complementary

Analogue Output Number	2	
Analogue Output Type	Voltage 010 V	
Analogue Output Resolution	12 bits	
Lsb Value	2.44 mV 010 V voltage	
Load Type	Resistive	
Load Impedance Ohmic	>= 2 kOhm	
Conversion Time	20 ms	
Stabilisation Time	40 ms	
Absolute Accuracy Error	+/- 1 % of full scale +/- 0.3 % of full scale at 77 °F (25 °C)	
Temperature Drift	+/- 0.02 %FS/°C	
Repeat Accuracy	+/- 0.4 %FS	
Non-Linearity	+/- 0.01 %FS	
Cross Talk	<= 1 LSB	
Type Of Cable	Twisted shielded pairs cable	
Electrical Connection	3 x 1.5 mm² 2 screw terminal blocks pitch 3.81 mm for outputs	
Maximum Cable Distance Between Devices	Twisted shielded pairs cable <98.43 ft (30 m) output	
Insulation	Non-insulated between analogue output and internal logic	
Height	1.61 in (41 mm)	
Depth	0.59 in (15 mm)	
Width	1.38 in (35 mm)	
Net Weight	0.03 lb(US) (0.015 kg)	

Environment

Immunity To Microbreaks 10 ms

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10MSX22533
Discount Schedule	OMSX
Gtin	3606480649103
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.38 in (3.5 cm)	
Package 1 Width	2.76 in (7.0 cm)	
Package 1 Length	1.81 in (4.6 cm)	
Package 1 Weight	0.71 oz (20.0 g)	
Unit Type Of Package 2	2 S02	
Number Of Units In Package 2	75	
Package 2 Height	5.91 in (15 cm)	
Package 2 Width	11.81 in (30 cm)	
Package 2 Length	15.75 in (40 cm)	
Package 2 Weight	7.40 lb(US) (3.356 kg)	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	1200	
Package 3 Height	29.53 in (75 cm)	
Package 3 Width	23.62 in (60 cm)	
Package 3 Length	31.50 in (80 cm)	
Package 3 Weight	165.35 lb(US) (75 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov