Product data sheet

Specifications



() Discontinued

automatic PowerLogic PFC Capacitor bank, with incoming CB 600V 60Hz 100kvar

VLVAW2N76100AB

Discontinued on: May 19, 2023

Product availability: Stock - Normally stocked in distribution facility

Main

Network Rated Voltage	600 V AC 60 Hz
Reactive Power Rating	100 kvar
Operating Mode	Automatic
Range Of Product	PowerLogic
Device Short Name	PowerLogic PFC standard
Product Or Component Type	Capacitor bank
Controller Type	PowerLogic PFC Controller VPL6
Capacitor Technology	PowerLogic PFC Capacitor
Accessibility For Operation	Front
Color	Gray RAL 7035)

Complementary

Network Pollution Level	No polluted	
[Thdv] Total Harmonic Distortion	03 %	
Power Per Step	25 kvar	
Step Composition	2x25 + 50	
Location Of Connection	Тор	
Internal Voltage Transformer	600/120 V	
Poles Description	3P	
Capacitance Tolerance	- 5 % to 10 %	
Maximum Permissible Voltage	1.1 x Un 8 hours over 24 hours)	
Protection Type	Circuit breaker protection	
Breaking Capacity	50 kA	
Control Type	Rotary handle	
Maximum Weight	165 lb(US) (74.84 kg) 165.35 lb(US) (75 kg)	
Height	33.46 in (850 mm) 33.5 in (850.90 mm)	
Width	31.50 in (800 mm) 31.5 in (800.10 mm)	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Depth

15.7 in (398.78 mm) 15.75 in (400 mm)

Mounting Location

Indoor

Environment

Standards	CSA C22.2 No 190-M1985 UL 810	
Mechanical Degree Of Protection	IK10	
Relative Humidity	095 %	
Operating Altitude	<= 6561.68 ft (2000 m)	
Ambient Air Temperature For Operation	14104 °F (-1040 °C)	
Average Ambient Air Temperature	30 °C annual)	

For Operation

Ordering and shipping details

Category	00085-VARSET VLV LV CAP BANK (CTO)	
Discount Schedule	DE2C	
Returnability	No	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Weight	150.00 lb(US) (68.039 kg)	

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov