Product data sheet

Specifications





die-cast empty control station, XAPG, grey, Ø22, 80x220mm front plate, 6 cut-outs

XAPG4506

- ! Discontinued on: Jun 30, 2022
- ! End-of-service on: Jul 28, 2022



Main

| Range Of Product | Harmony XAP | |
|---------------------------------------|--|--|
| Product Or Component Type | Die-cast empty control station | |
| Device Short Name | XAPG | |
| Product Destination | For Ø 22 mm control and signalling units | |
| Product Front Plate Size | 80 x 220 mm | |
| Usable Depth | 2.93 in (74.5 mm) | |
| Number Of Cut-Out | 6 cut-outs | |
| Colour Of Base Of Enclosure | Grey RAL 7032) | |
| Colour Of Cover | Grey RAL 7032) | |
| Material | Zinc alloy | |
| Product Mounting | Flush mounting | |
| p Degree Of Protection IP65 IEC 60529 | | |

Complementary

| Number Of Vertical Rows | 1 | |
|-------------------------|--|--|
| Cable Entry | 0.71 in (18 mm) 1 hole without blanking plug for cable gland | |
| Net Weight | 3.04 lb(US) (1.38 kg) | |
| Compatibility Code | XAPG | |

Environment

| Protective Treatment | тн |
|---------------------------------------|---------------------------------------|
| mbient Air Temperature For torage | -40158 °F (-4070 °C) |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Electrical Shock Protection Class | Class I IEC 60536 Class I NF C 20-030 |

Ordering and shipping details

| Category | 18406-WORLD SERVICE PARTS(OTHER OP INT) |
|-------------------|---|
| Discount Schedule | CS2 |
| Gtin | 3389110890600 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability No

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |