

# Product data sheet

Specifications



Small panel with keypad, matrix screen, green, 122 x 32 pixels, 24V DC

XBTR410

⚠ Discontinued on: Feb 17, 2021

⚠ End-of-service on: Dec 23, 2022

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range Of Product	Magelis XBTR
Display Resolution	122 x 32 pixels
Software Type	Configuration software
Software Designation	Vijeo Designer Lite
Operating System	Windows

## Complementary

Display Type	Matrix backlit LCD
Character Font	Latin Katakana Greek Cyrillic Chinese (simplified Chinese)
Supply Voltage Limits	18...30 V
Residual Ripple	<= 1200 mV
Power Consumption In W	5 W
Number Of Key	20
Number Of Fixed Keys	8
Number Of Customisable Keys	12
Number Of Pages	256 alarm pages 200 application pages
Memory Type	Flash
Memory Capacity	512 KB
Integrated Connection Type	Serial link female SUB-D 25, asynchronous RS232C/RS485)multidrop Power supply removable screw terminal block
Realtime Clock	Access to the PLC real-time clock
Range Compatibility	Twido Modicon TSX Micro Modicon Quantum Modicon Momentum Modicon Premium Modicon M340
Product Mounting	Flush mounting
Fixing Mode	By 4 spring clips

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Display Material	Polyester
Front Material	PPT
Keypad Material	Polyester
Marking	CE
Height	4.65 in (118 mm)
Width	5.39 in (137 mm)
Depth	1.54 in (39 mm)
Cut-Out Dimensions	119.6 (+/- 0.5) x 105.2 (+/- 0.4) mm
Net Weight	1.21 lb(US) (0.55 kg)

## Environment

Product Or Component Type	Small panel with keypad
Display Colour	Green
Display Capacity	1 line of 5 characters minimum 4 lines of 20 characters maximum
[Us] Rated Supply Voltage	24 V DC
Supply	External source
Downloadable Protocols	Third party protocols Modbus Uni-TE
Standards	UL 508 IEC 60068-2-27 IEC 60068-2-6 IEC 61131-2 CSA C22.2 No 14
Product Certifications	CSA Class 1 Division 2 ATEX zone 2/22 UL Class 1 Division 2 UL 1604
Ambient Air Temperature For Operation	32...131 °F (0...55 °C)
Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C)
Relative Humidity	0...85 % without condensation
Ip Degree Of Protection	IP20 IEC 60529 rear panel) IP65 IEC 60529 front panel)
Nema Degree Of Protection	NEMA 4X front panel outdoor use)
Shock Resistance	15 gn 11 ms
Vibration Resistance	+/- 3.5 mm 2...8.45 Hz) 1 gn 8.45...150 Hz)

## Ordering and shipping details

Category	US10MC222570
Discount Schedule	0MC2
Gtin	3389119000048
Returnability	No
Country Of Origin	CN

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.89 in (4.8 cm)
Package 1 Width	6.89 in (17.5 cm)
Package 1 Length	9.84 in (25.0 cm)
Package 1 Weight	21.27 oz (603.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	14.74 lb(US) (6.686 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Dimensions Drawings


Dimensions



a		a1 (1)		b		b1 (1)		P3 (2)		P4 (3)	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
137	5.39	160	6.29	118	5	146	6	58	2.28	104	4.09
<div>(1) With fixing clips (included with product)</div> <div>(2) P3: depth with 25-way SUB-D angled cable XBTZ9680 (for Twido, TSX Micro and Premium) or XBTZ998 (for Modicon STB)</div> <div>(3) P4: depth with 25-way SUB-D cable XBTZ68/Z9681(for Twido, TSX Micro and Premium)</div>											

Mounting and Clearance

Cut-out for Flush Mounting



Panel thickness = 1.5...6 mm / 0.05...0.23 in.

H		G		r max.	
±0.4 mm	±0.02 in.	±0.5 mm	±0.02 in.	mm	in.
105.2	4.14	119.6	5	1.5	0.05