

# Product data sheet

Specifications



## complete joystick controller XKB - mounting diameter 30mm

XKBA1111

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range Of Product	Harmony XK
Product Or Component Type	Complete joystick controller
Product Specific Application	Light hoisting applications

### Complementary

Device Short Name	XKB
Bezel Material	Metal
Fixing Collar Material	Metal
Sale Per Indivisible Quantity	1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-4...158 °F (-20...70 °C)
Overvoltage Category	Class I IEC 61140
Ip Degree Of Protection	IP54 IEC 60529 IP20 IEC 60529
Standards	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14
Product Certifications	RRS UL CSA CCC
Contact Code Designation	A300 Q300
Operator Position Information	All positions
Operator Profile	Standard handle
Notch Per Direction	1...3 12°-20°-28° for each direction
Mechanical Durability	1000000 cycles
Vibration Resistance	6 gn 1...70 Hz)IEC 60068-2-6
Shock Resistance	20 gn 11 ms) IEC 60068-2-27
Connections - Terminals	Captive screw clamp terminals, <= 2 x 1.5 mm² with cable end Captive screw clamp terminals, <= 1 x 2.5 mm² without cable end Captive screw clamp terminals, >= 1 x 0.5 mm²

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Short-Circuit Protection	10 A cartridge fuse gG EN/IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A EN/IEC 60947-5-1 10 A CSA C22.2 No 14 10 A UL 508
[Ui] Rated Insulation Voltage	500 V 3)IEC 60947-1
Compatibility Code	XKB

## Ordering and shipping details

Category	US1000I22474
Discount Schedule	000I
Gtin	3303431826346
Returnability	No
Country Of Origin	FR

## Contractual warranty

Warranty	18 months
----------	-----------