

Product data sheet

Specifications



Complete joystick controller, Harmony XK, XKBA, 2 movements, 4 directions

XKBA14200

⚠ Discontinued on: Jan 23, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XK
Product Or Component Type	Complete joystick controller
Product Specific Application	Light hoisting applications

Complementary

Device Short Name	XKB
Bezel Material	Metal
Fixing Collar Material	Metal
Sale Per Indivisible Quantity	1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-4...158 °F (-20...70 °C)
Overvoltage Category	Class I IEC 61140
Ip Degree Of Protection	IP54 IEC 60529 IP20 IEC 60529
Standards	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14
Product Certifications	RRS UL CSA CCC
Contact Code Designation	Q300 A300
Operator Position Information	All positions
Operator Profile	Handle with zero position mechanical interlock
Notch Per Direction	1...3 12°-20°-28° for each direction
Mechanical Durability	1000000 cycles
Vibration Resistance	6 gn 1...70 Hz)IEC 60068-2-6
Shock Resistance	20 gn 11 ms) IEC 60068-2-27
Connections - Terminals	Captive screw clamp terminals, <= 2 x 1.5 mm² with cable end Captive screw clamp terminals, <= 1 x 2.5 mm² without cable end Captive screw clamp terminals, >= 1 x 0.5 mm²
Short-Circuit Protection	10 A cartridge fuse gG EN/IEC 60947-5-1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ith] Conventional Free Air Thermal Current	10 A EN/IEC 60947-5-1 10 A CSA C22.2 No 14 10 A UL 508
[Ui] Rated Insulation Voltage	500 V 3)IEC 60947-1

Ordering and shipping details

Category	US1000I22474
Discount Schedule	000I
Gtin	785901543671
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.50 in (24.13 cm)
Package 1 Width	6.50 in (16.51 cm)
Package 1 Length	6.40 in (16.256 cm)
Package 1 Weight	32.00 oz (907.185 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration