

Product data sheet

Specifications



Complete pre wired monolithic tower light, Harmony XVC, plastic, red, 40mm, tube mounting, steady or flashing, buzzer, IP23, 24V AC DC

XVC4B15S

Product availability: Stock - Normally stocked in distribution facility

Price*: 240.00 USD

Main

Range Of Product	Harmony XVC4
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	1 illuminated unit
Sound Signalling	Buzzer
Mounting Diameter	1.57 in (40 mm)
Component Name	XVC
Device Short Name	XVC
Light Source	LED steady or flashing red
Supply Circuit Type	AC/DC
Noise Level	70...85 dB continuous or intermittent tone)1 m

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover SGP (chromium-plated): support tube
Mounting Location	On support tube, 17 mm
Product Mounting	On support tube, 17 mm
[Us] Rated Supply Voltage	24 V
[Us] Rated Supply Voltage	24 V
Cable Cross Section	0.00 in² (0.33 mm²)
Awg Gauge	AWG 22
Cable Length	35.43 in (900 mm)
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	65 mA
Fundamental Frequency	2.23 kHz
Flashing Frequency	1 Hz
Net Weight	1.32 lb(US) (0.6 kg)
Height	20.65 in (524.5 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61000-6-3 IEC 61000-6-2
Product Certifications	UL
Protective Treatment	TC
Ambient Air Temperature For Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature For Operation	14...122 °F (-10...50 °C)
Electrical Shock Protection Class	Class I IEC 61140
Overvoltage Category	Class I IEC 61140
Ip Degree Of Protection	IP23 vertical surface installation IEC 60529

Ordering and shipping details

Category	US100XV22617
Discount Schedule	00XV
Gtin	3606480032479
Returnability	Yes
Country Of Origin	ID

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.000 cm)
Package 1 Width	29.53 in (75.000 cm)
Package 1 Length	2.76 in (7.000 cm)
Package 1 Weight	23.84 oz (676.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.69 in (17.000 cm)
Package 2 Width	14.17 in (36.000 cm)
Package 2 Length	30.31 in (77.000 cm)
Package 2 Weight	17.00 lb(US) (7.713 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	30
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	68.65 lb(US) (31.139 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65


WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b1** dimension.



No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	524.50	20.65
2 stages	559.50	22.03
3 stages	594.50	23.41
4 stages	629.50	24.78
5 stages	664.50	26.16

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting

