# Product data sheet

Specifications





Head for pilot light, Harmony XAC, for incandescent bulb, plastic, green cap, 22mm

ZA2BV03

Product availability: Stock - Normally stocked in distribution

Price\*: 9.60 USD

#### Main

Range Of Product	Harmony
Product Or Component Type	Head for pilot light
Product Specific Application	For incandescent bulb
Cap/Operator Or Lens Colour	Green

### Complementary

Mechanical Durability	1000000 cycles
Net Weight	0.03 lb(US) (0.015 kg)
Compatibility Code	ZA2B

#### **Environment**

Standards	CSA C22.2 No 14 EN/IEC 60947-5-1	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-13131 °F (-2555 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6	
Shock Resistance	100 gn IEC 60068-2-27	
Electrical Shock Protection Class	Class II IEC 61140	
Overvoltage Category	gory Class II IEC 61140	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK08 conforming to EN 50102	

### Ordering and shipping details

Category	US10CS222460	
Discount Schedule	0CS2	
Gtin	3389110645361	
Returnability	Yes	
Country Of Origin	FR	

### **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	1.57 in (4.0 cm)
Package 1 Weight	0.53 oz (15.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.97 in (5.0 cm)
Package 2 Width	6.69 in (17.0 cm)
Package 2 Length	5.91 in (15.0 cm)
Package 2 Weight	5.36 oz (152.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	3.76 lb(US) (1.705 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov