


Product data sheet

Specifications



red Ø40 mushroom head emergency stop - Ø22

ZB2BC4

 **Discontinued on:** Dec 19, 2019

 **Discontinued**

Main

Range Of Product	Harmony XB2
Product Or Component Type	Mushroom head push-button
Device Short Name	ZB2
Bezel Material	Zamak
Mounting Diameter	0.87 in (22 mm)
Sale Per Indivisible Quantity	1

Complementary

Product Compatibility	XB2.
Mounting Location	Panel
Shape Of Signaling Unit Head	Round
Type Of Operator	Spring return spring return
Operator Profile	Red mushroom Ø 40 mm, unmarked
Mechanical Durability	3000000 cycles
Height	1.57 in (40 mm)
Width	1.57 in (40 mm)
Depth	1.89 in (48 mm)
Net Weight	0.10 lb(US) (0.045 kg)

Environment

Protective Treatment	TC/TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Standards	GB/T 14048.5 EN/IEC 60947-5-1 GB/T 14048.1 EN/IEC 60947-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 GB/T 14048.14
Product Certifications	CCC CE
Vibration Resistance	8 gn 40...500 Hz)IEC 60068-2-6
Shock Resistance	15 gn 11 ms) half sine wave acceleration IEC 60068-2-27

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	22461-PUSHBUTTON, 22MM_(METAL)
Discount Schedule	CS2
Gtin	00785901249344
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------