

Product data sheet

Specifications



body for pilot light - zb2 - clear bulb ba 9s - 400 v

ZB2BV5

 **Discontinued on:** Mar 31, 2020

 **Discontinued**

Main

Range Of Product	Harmony XB4
Product Or Component Type	Complete body/light block assembly
Device Short Name	ZB4
Sale Per Indivisible Quantity	1
Light Source	Incandescent

Complementary

Fixing Collar Material	Zamak
Cad Overall Width	1.18 in (30 mm)
Cad Overall Height	1.85 in (47 mm)
Cad Overall Depth	2.36 in (60 mm)
Terminals Description Iso N°1	(X1-X2)PL
Net Weight	0.29 lb(US) (0.131 kg)
Overvoltage Category	Class I IEC 60536
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end
Tightening Torque	7.08...10.62 lbf.in (0.8...1.2 N.m) EN 60947-1
Shape Of Screw Head	Cross Philips no 1
[Ui] Rated Insulation Voltage	600 V 3)EN 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV EN 60947-1
Signalling Type	Steady
Bulb Base	BA 9s
Light Block Supply	Via integral transformer 1.2 VA 6 V
[Us] Rated Supply Voltage	400 V AC 50/60 Hz
Mounting Of Block	Front mounting
Electrical Composition Code	P4

Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...131 °F (-25...55 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
Standards	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-5-5 EN/IEC 60947-1 JIS C 4520 EN/IEC 60947-5-4
Product Certifications	RINA BV DNV CSA GL LROS (Lloyds register of shipping) UL Listed
Vibration Resistance	5 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	22461-PUSHBUTTON, 22MM_(METAL)
Discount Schedule	CS2
Gtin	00785901253068
Returnability	No
Country Of Origin	ES

Contractual warranty

Warranty	18 months
----------	-----------