# Product data sheet

Specifications





Head for push button, Harmony XB4, harsh environment, metal, light blue, 22mm,Vertical mounting, marked type h005

ZB4BC98005

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 36.60 USD

#### Main

Range Of Product	Harmony XB4	
Product Or Component Type	Head for push-button	
Device Short Name	ZB4	
Bezel Material	Chromium plated metal	
Head Type	Standard	
Mounting Diameter	0.89 in (22.5 mm)	
Sale Per Indivisible Quantity	1	
Cap/Operator Or Lens Colour	Light blue	

### Complementary

eempromentary		
Cad Overall Width	1.46 in (37 mm)	
Cad Overall Height	0.73 in (18.5 mm)	
Cad Overall Depth	1.46 in (37 mm)	
Net Weight	0.08 lb(US) (0.036 kg)	
Electrical Shock Protection Class	Class I IEC 61140	
Shape Of Signaling Unit Head	Round	
Type Of Operator	spring return	
Operator Profile	Light blue flush, type H005 white)	
Operator Additional Information	Vertical mounting	
Mechanical Durability	1000000 cycles	
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27	
Main Group	Harsh environment	
Group Of Product	Flush marked type H005	
Marking	Туре Н005	
Colour Of Marking	White	
Electrical Composition Code	C1 9 single front mounting C2 9 single and double front mounting C11 3 single front mounting C15 1 single front mounting	

C15 1 single front mounting

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

### Environment

Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Ip Degree Of Protection	IP66 IEC 60529 IP69K IP67 IP69
Nema Degree Of Protection	NEMA 4 UL 508 NEMA 13 NEMA 12
Resistance To High Pressure Washer	0.01 psi (90 Pa) 180 °F (82.5 °C)
Ik Degree Of Protection	IK06 conforming to IEC 62262
Standards	IEC 60947-5-1 IEC 60947-1 UL 508 CSA C22.2
Product Certifications	CSA CE UL

# Ordering and shipping details

Category	US10CS222468
Discount Schedule	0CS2
Gtin	3606480444777
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.48 in (3.76 cm)
Package 1 Width	1.46 in (3.7 cm)
Package 1 Length	1.46 in (3.7 cm)
Package 1 Weight	1.16 oz (33.0 g)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov