# Product data sheet

Specifications





Head for key selector switch, Harmony XB4, Ø22 mm

ZB4BG0310

() Discontinued on: Jun 30, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

mann		
Range Of Product	Harmony XB4	
Product Or Component Type	Head for key selector switch	
Device Short Name	ZB4	
Mounting Diameter	0.87 in (22 mm)	
Head Type	Standard	
Sale Per Indivisible Quantity	1	
Shape Of Signaling Unit Head	Round	
Operator Profile	key switch	

### Complementary

Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
Mechanical Durability	1000000 cycles
Electrical Composition Code	C3 6 single front mounting
	C4 6 single and double front mounting
	C5 5 single front mounting
	C6 5 single and double front mounting
	C7 4 single front mounting
	C8 4 single and double front mounting
	C11 3 single front mounting
Device Presentation	Basic element

### Environment

Protective Treatment	ТН	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	
Overvoltage Category	Class I IEC 60536	
Ip Degree Of Protection	IP66 IEC 60529 IP67 IP69 IP69K	
Nema Degree Of Protection	NEMA 13	
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10CS222468
Discount Schedule	0CS2
Gtin	3389110222135
Returnability	No
Country Of Origin	МХ

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.46 in (8.8 cm)
Package 1 Width	1.34 in (3.4 cm)
Package 1 Length	2.13 in (5.4 cm)
Package 1 Weight	2.43 oz (69.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	12.47 lb(US) (5.655 kg)

#### **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov