# Product data sheet





### Light block for head 22mm, Harmony XB4, blue, integral LED, 110...120V AC

ZBVG6

! Discontinued on: Jan 9, 2023

(!) Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Important message: All colored LED are replaced with a single Universal LED block for use with new illuminated heads (more information at se.com/harmonyxb4 or se.com/harmonyxb5)

#### Main

Range Of Product	Harmony XB4 Harmony XB5
Product Or Component Type	Light block
Device Short Name	ZBV
Sale Per Indivisible Quantity	5
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end EN 60947-1 Screw clamp terminals, >= 1 x 0.22 mm² without cable end EN 60947-1
Signalling Type	Steady
Light Source	Protected LED
Bulb Base	Integral LED
Light Block Supply	Direct
Light Source Colour	Blue
[Us] Rated Supply Voltage	110120 V AC 50/60 Hz

### **Complementary**

•	•
Net Weight	0.04 lb(US) (0.017 kg)
Tightening Torque	7.0810.62 lbf.in (0.81.2 N.m) EN 60947-1
Shape Of Screw Head	Cross Philips no 1 Cross pozidriv No 1 Slotted flat Ø 4 mm Slotted flat Ø 5.5 mm
Current Consumption	14 mA
Service Life	100000 h at rated voltage and 25 °C
Surge Withstand	1 kV IEC 61000-4-5
Mounting Of Block	Front mounting

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

	PF1
	P2
	P1
	MF1
	M10
	M6
	M5
	M4
	M3
	M2
Electrical Composition Code	M1

### **Environment**

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Ip Degree Of Protection	IP20 IEC 60529
Standards	UL 508 CSA C22.2 No 14 EN/IEC 60947-5-5 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C8201-5-1 EN/IEC 60947-1 JIS C8201-1
Product Certifications	CSA UL Listed
Resistance To Fast Transients	2 kV IEC 61000-4-4
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3
Resistance To Electrostatic Discharge	6 kV on contact (on metal parts) IEC 61000-4-2 8 kV in free air (in insulating parts) IEC 61000-4-2
Electromagnetic Emission	Class B IEC 55011
[Us] Rated Supply Voltage	110120 V

# Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
Gtin	3389110089998
Returnability	Yes
Country Of Origin	FR

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.6 cm)
Package 1 Width	1.73 in (4.4 cm)
Package 1 Length	2.13 in (5.4 cm)
Package 1 Weight	0.32 oz (9.0 g)
Unit Type Of Package 2	BB1

Number Of Units In Package 2	5
Package 2 Height	2.20 in (5.6 cm)
Package 2 Width	1.73 in (4.4 cm)
Package 2 Length	2.13 in (5.4 cm)
Package 2 Weight	1.83 oz (52.0 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	800
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	19.74 lb(US) (8.955 kg)

# **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information


Apr 26, 2024

### ZBVG6

### **Dimensions Drawings**

#### **Dimensions**

#### with ZB5AZ009 Fixing Collar



### with ZB4BZ009 Fixing Collar

