# **Product data sheet**

Specification





Light block, Harmony XB4 XB5, white, for head 22mm, universal LED, screw clamp terminals, 12V AC DC

ZBVJ1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 52.00 USD

#### Main

Range Of Product	Harmony XB5 Harmony XB4
Product Or Component Type	Light block
Device Short Name	ZBV
Sale Per Indivisible Quantity	5
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm² with cable end IEC 60947-1 Screw clamp terminals, >= 1 x 0.22 mm² without cable end IEC 60947-1
Signalling Type	Steady
Light Source	Universal LED
Bulb Base	Integral LED
Light Block Supply	Direct
Light Source Colour	White
[Us] Rated Supply Voltage	12 V AC/DC 50/60 Hz

#### Complementary

Net Weight	0.04 lb(US) (0.017 kg)	
Tightening Torque	7.0810.62 lbf.in (0.81.2 N.m) IEC 60947-1	
Shape Of Screw Head	Cross Philips no 1 Cross pozidriv No 1 Slotted flat Ø 4 mm Slotted flat Ø 5.5 mm	
Supply Voltage Limits	1015 V DC 10.213.8 V AC	
Current Consumption	15 mA	
Service Life	100000 h at rated voltage and 25 °C	
Surge Withstand	1 kV IEC 61000-4-5	
Mounting Of Block	Front mounting	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical Composition Code	M1
	M2
	M3
	M4
	M5
	M6
	M10
	MF1
	P1
	P2
	PF1
Device Presentation	Basic element

### **Environment**

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Ip Degree Of Protection	IP20 IEC 60529
Standards	JIS C8201-5-1 IEC 60947-1 IEC 60947-5-5 UL 508 IEC 60947-5-1 IEC 60947-5-4 CSA C22.2 No 14 JIS C8201-1
Product Certifications	UL Listed CSA
Resistance To Fast Transients	2 kV IEC 61000-4-4
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3
Resistance To Electrostatic Discharge	6 kV on contact (on metal parts) IEC 61000-4-2 8 kV in free air (in insulating parts) IEC 61000-4-2
Electromagnetic Emission	Class B IEC 55011
[Us] Rated Supply Voltage	12 V

## Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
Gtin	3389110069907
Returnability	Yes
Country Of Origin	FR

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.6 cm)
Package 1 Width	1.73 in (4.4 cm)
Package 1 Length	2.13 in (5.4 cm)
Package 1 Weight	0.32 oz (9 g)
Unit Type Of Package 2	BB1

Number Of Units In Package 2	5
Package 2 Height	2.20 in (5.6 cm)
Package 2 Width	1.73 in (4.4 cm)
Package 2 Length	2.13 in (5.4 cm)
Package 2 Weight	1.80 oz (51 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	400
Package 3 Height	5.91 in (15 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	9.63 lb(US) (4.37 kg)

## **Contractual warranty**

Warranty 18 months

### Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	· · · · · · · · · · · · · · · · · · ·

#### ZBVJ1

#### **Dimensions Drawings**

#### **Dimensions**

#### with ZB5AZ009 Fixing Collar



#### with ZB4BZ009 Fixing Collar

