

Product datasheet

Specifications



FRONT PLATE CVS 630 VERTICAL FIXED TOGGLE W300 8M

03280

Discontinued on: Apr 13, 2023

Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct
Type Of Front Plate	Cut-out
Type Of Front Plate	Cut-out
Installed Device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - vertical installation
Poles Description	1 x 3P: mounting plate support: CVS400 vertical installation 1 x 4P: mounting plate support: CVS400 vertical installation 1 x 3P: mounting plate support: CVS630 vertical installation 1 x 4P: mounting plate support: CVS630 vertical installation
Operating Position	Vertical

Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	8
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	400 mm
Width	300 mm
Net Weight	0.86 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed toggle vertical
	3P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed toggle vertical
	3P 1 direct with long terminal shield 12
	300 mm Prisma G floor-standing duct EasyPact CVS400 without fixed toggle vertical
	4P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct EasyPact CVS400 without fixed toggle vertical
	4P 1 direct with long terminal shield 12
	300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed toggle vertical
	3P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed toggle vertical
	3P 1 direct with long terminal shield 12
	300 mm Prisma G floor-standing duct EasyPact CVS630 without fixed toggle vertical
	4P 1 direct with long terminal shield 12
	300 mm Prisma G wall-mounted duct EasyPact CVS630 without fixed toggle vertical
	4P 1 direct with long terminal shield 12

Environment

Ip Degree Of Protection	IP30
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	26.000 cm
Package 1 Length	41.000 cm
Package 1 Weight	860.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	27.000 cm
Package 2 Length	44.000 cm
Package 2 Weight	8.960 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	180
Package 3 Height	66.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	161.280 kg

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile