

Product datasheet

Specifications



Mini Pragma surface enclosure - IP 40 - 1 x 6 modules - opaque door

13377

 **Discontinued on:** Jan 23, 2021

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	6
Nb Of Horizontal Rows	1
Provided Equipment	1 marking kit 1 insulating plug 2 terminal block support 2 earth-neutral terminal blocks 4 holes
Type Of Door	Opaque
Width	148 mm
Height	200 mm
Depth	94 mm

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	12
Total Number Of 18 Mm Modules	6
[In] Rated Current	63 A
[Ui] Rated Insulation Voltage	690 V
Type Of Rail	DIN
Number Of Terminal Blocks	2 neutral / earth (Quick) with 4 outgoers
Distribution Block Outgoers	4 x 10 mm ² for earth / neutral 4 x 16 mm ² for earth / neutral
Locking Options Description	Keylock option
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	IEC 60695-2-1 EN 60439-3 EN 50102 IEC 60529 IEC 60439-3
-----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	15 cm
Package 1 Length	20 cm
Package 1 Weight	0.49 kg

Contractual warranty

Warranty	18 months
----------	-----------