Product datasheet

Specification





miniature circuit breaker - iK60N - 1P - 20 A - C curve

A9K17120

Main

Device Application	Distribution	
Range	Acti9	
Product Name	Acti9 iK60	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	iK60N	
Poles Description	1P	
Number Of Protected Poles	1	
[In] Rated Current	20 A at 30 °C	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	С	
Breaking Capacity	6000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1	
Suitability For Isolation	Yes conforming to EN/IEC 60898-1	
Standards	EN/IEC 60898-1	
Product Certifications	AENOR	

Complementary

Network Frequency	50/60 Hz	
Magnetic Tripping Limit	510 x ln	
[Ics] Rated Service Breaking Capacity	6000 A 100 % conforming to EN/IEC 60898-1 - 230 V AC 50/60 Hz	
Limitation Class	3 conforming to EN/IEC 60898-1	
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60898-1	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
9 Mm Pitches	2	
Height	85 mm	
Width	18 mm	
Depth	78.5 mm	

Net Weight	100 g
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Tunnel type terminal (top or bottom) 125 mm² rigid Tunnel type terminal (top or bottom) 116 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	2 conforming to EN/IEC 60898-1
Overvoltage Category	III
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.3 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	99.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.1 cm
Package 2 Width	9.8 cm
Package 2 Length	22.4 cm
Package 2 Weight	1.247 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	132
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	14.205 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations