# **Product datasheet**





Acti9 - fuse-disconnector STI - 1 pole + N - 25 A - for fuse 10.3 x 38 mm

A9N15646

#### Main

Range	Acti9	
Product Name	Acti9 STI	
Product Or Component Type	Fuse-disconnector	
Device Short Name	STI	
Poles Description	1P + N	

## Complementary

[In] Rated Current	2 A
	4 A
	6 A
	10 A
	16 A
	20 A
	25 A
Fuse Curve	AM
	GG
Fuse Size	10.3 x 38 mm
[Ue] Rated Operational Voltage	500 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	75 mm
Colour	White
Connections - Terminals	Screw clamp terminals1 cable(s) 0.7510 mm² rigid
	Screw clamp terminals1 cable(s) 0.56 mm² flexible
	Screw clamp terminals2 cable(s) 0.754 mm² rigid
	Screw clamp terminals2 cable(s) 0.56 mm² flexible
Wire Stripping Length	12 mm
Tightening Torque	2 N.m

## **Environment**

Standards	IEC 60269-1/2 IEC EN 60947-3
Ip Degree Of Protection	IP20

Pollution Degree	3
Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4080 °C

# **Packing Units**

racking office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.700 cm
Package 1 Width	7.600 cm
Package 1 Length	8.000 cm
Package 1 Weight	73.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	2.730 cm
Package 2 Width	30.000 cm
Package 2 Length	20.000 cm
Package 2 Weight	927.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	11.661 kg



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information Yes	
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations