## **Product datasheet**

Specification





# Acti 9 iID K - residual current circuit breaker - 2P - 40A - 30mA - type AC

A9R50240

#### Main

Range	Acti9
Product Name	Acti9 iID K
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	ilD K
Poles Description	2P
Neutral Position	Left
[In] Rated Current	40 A
Network Type	AC
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type AC
Quality Labels	VDE

### Complementary

Device Location In System	Outgoer
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	220240 V AC 50/60 Hz
Residual Current Tripping Technology	Voltage independent
Rated Breaking And Making Capacity	ldm 500 A Im 500 A
Rated Conditional Short-Circuit Current	GL63: Inc 4.5 kA K60: Inc 6 kA C60: Inc 6 kA
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Surge Current	250 A
Contact Position Indicator	No
Control Type	Toggle
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	85 mm

Width	36 mm
Depth	69 mm
Net Weight	0.21 kg
Colour	White
Mechanical Durability	5000 cycles
Electrical Durability	AC-1: 2000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Tunnel type terminals top or bottom 135 mm² rigid Tunnel type terminals top or bottom 125 mm² flexible Tunnel type terminals top or bottom 125 mm² flexible with ferrule
Wire Stripping Length	16 mm for top or bottom connection
Tightening Torque	3.5 N.m top or bottom

#### **Environment**

Standards	EN/IEC 61008-1 EN/IEC 61008-2-1
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	2
Electromagnetic Compatibility	8/20 µs impulse withstand, 200 A conforming to EN/IEC 61008-1
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-4085 °C

## **Packing Units**

r doming office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	8.5 cm
Package 1 Length	10 cm
Package 1 Weight	208 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	10.5 cm
Package 2 Length	25.5 cm
Package 2 Weight	1.343 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	54
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.358 kg

## **Contractual warranty**

Warranty

Apr 25, 2024

18 months

## Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations