

Product datasheet

Specifications



AS-Interface - premounted in emergency stop station XALK - turn to release

ASISEA1C

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Product Or Component Type	Interface premounted in emergency stop station XALK
Range Compatibility	AS-Interface cabling system
Type Of Operator	Turn to release
Number Of Contacts	2
Actuator Sensor Interface Profile [As-I]	0.B.F.F
Supply	Via AS-Interface

Complementary

Addressing	Using adjustment terminal
[Us] Rated Supply Voltage	24 V DC - 15...15 %
Power Consumption In W	1.2 W
Current Consumption	45 mA for AS-Interface line
Connections - Terminals	For AS-Interface line: 1 connector M12
Mechanical Durability	300000 cycles
Net Weight	0.17 kg

Environment

Standards	EN/IEC 60947-5-3 EN/IEC 61496-1 EN 1088/ISO 14119 EN/ISO 13850 ISO 13849-1 category 4 EN/IEC 60204-1 EN/ISO 12100 EN 954-1 category 4
Product Certifications	UL CSA
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ambient Air Temperature For Operation	-10...55 °C
Ambient Air Temperature For Storage	-25...85 °C
Vibration Resistance	5 gn
Shock Resistance	10 gn

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months