



13A 250V 1 Gang Switched Socket with Neon, Wine Gold

E8215N_WG_G1

Main

Range	Pieno	
Product Or Component Type	Power socket-outlet	
Switch Function	Switch	
Rated Current	13 A at 250 V AC 5060 Hz	
Number Of Gangs	1 gang	
Load Type	Resistive	
Cover Frame Colour Tint	Frame Colour Tint Wine gold	

Complementary

Wiring Device Mounting	Flush Surface	
Material	Polycarbonate: surround Polycarbonate: grid plate	
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)	
Width	87 mm	
Height	87 mm	
Depth	26.6 mm	

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	MS 589-2
	SS 145-2
	BS 1363-2

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations