

Product datasheet

Specifications



Pieno - 45A 250V - 1 gang double pole switch with neon (MB)

E8231D45N_MB

Main

Range of product	Pieno
Product or component type	Switch
Switch application	Switch
Rated current	45 A at 250 V AC 50 Hz
Local signalling	Neon
Number of gangs	1 gang
Load type	Fluorescent Resistive

Complementary

Wiring device mounting	Surface Flush
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	Pillar terminals
Clamping connection capacity	1 x 16 mm ² for solid cable(s) 1 x 10 mm ² for stranded cable(s)
Width	87 mm
Height	87 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1
Product certifications	CCC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	185.45 g
Package 1 Height	3.55 cm

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm

Recommended replacement(s)