

# Product datasheet

Specifications



## Easy9 - flush mounting enclosure 4 modules with smoked door - E+N term blocks

EZ9E0104

⚠ Discontinued on: May 19, 2023

⚠ Discontinued

### Main

Range	Easy9
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Provided Equipment	Box 1 x earth terminal block 1 x neutral terminal block Door
Nb Of 18 Mm Modules Per Row	4

### Complementary

Enclosure Mounting	Flush
Type Of Rail	DIN
Type Of Installation	Indoor
Number Of Pre-Cutouts Pg Iso	8
Terminal Block Function	Neutral Earth
Cable Entry	Pre-cutted holes
Type Of Door	Smoked
Door Opening Side	Upwards (100 °)
Lock Type	Push-close
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	400 V AC
[Uimp] Rated Impulse Withstand Voltage	2.5 kV
[Ui] Rated Insulation Voltage	500 V
Enclosure Material	Enclosure: self-extinguishing plastic
Width	136 mm external:
Height	222 mm external:
Depth	92 mm external:
Colour	White (RAL 9003)
Targeted Country	Vietnam

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-3
Fire Resistance	650 °C ( 1800 s ) conforming to IEC 60695-2-10
Ip Degree Of Protection	IP40 conforming to IEC 60529 (closed door) IP30 conforming to IEC 60529 (open door)
Ik Degree Of Protection	IK07 conforming to IEC 62262
Electrical Insulation Class	Class II
Ambient Air Temperature For Operation	-5...50 °C
Ambient Air Temperature For Storage	-15...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.2 cm
Package 1 Width	22.2 cm
Package 1 Length	13.6 cm
Package 1 Weight	440 g