

Product datasheet

Specifications



S-Flexi - 13A International socket, M size

F1426UAM_WE

Main

Range	S-Flexi
Product or component type	Socket-outlet
Device application	Power supply

Complementary

Colour tint	White
Quantity per set	1
Type of packing	Plastic bag
Material	PC (polycarbonate)
[In] rated current	13 A
[Ue] rated operational voltage	250 V AC 50/60 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Socket number	1
Installation direction	Horizontal/vertical
Device mounting	Flush
Connections - terminals	3 x screw terminal

Environment

Standards	IEC 60884
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	38 g
Package 1 Height	2.5 cm
Package 1 Width	3.5 cm

Package 1 Length	4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	32
Package 2 Weight	1216 g
Package 2 Height	8 cm
Package 2 Width	12.5 cm
Package 2 Length	18 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	320
Package 3 Weight	12250 g
Package 3 Height	21 cm
Package 3 Width	27 cm
Package 3 Length	43 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Recommended replacement(s)