# **Product datasheet**

Specifications

Sreen Premium™



# S-Flexi - 16A 250V 2 way switch, M size - White

F50\_2M2\_WE

() Discontinued on: Oct 9, 2023

(!) Discontinued

#### Main

Range	S-Flexi
Product Or Component Type	Switch
Wiring Device Mounting	Flush
Switch Function	2-way
Switch Application	On/off switching
Load Type	Light
Colour Tint	White

### Complementary

Rated Current	16 A at 250 V AC 50/60 Hz
Number Of Gangs	2 gangs horizontal
Material	PC (polycarbonate): wall
Clamping Connection Capacity	0.51.5 mm <sup>2</sup> for solid or flexible cable(s)
Connections - Terminals	Pillar terminals
Width	46.55 mm
Height	34.95 mm
Depth	34.97 mm

#### Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Standards	IEC 60669-1

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	3.5 cm
Package 1 Length	3.5 cm
Package 1 Weight	24 g

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information