Product datasheet

Specifications





Thorsman - Cable reel 20m HO5VVF 3G1.5 IP20 Contour

IMT33142

Main

·····	
Range	Thorsman
Range Of Product	PROchantier
Product Name	Thorsman cable reel Classic
Product Or Component Type	Extension cable reel
Device Application	Power supply
[Ue] Rated Operational Voltage	230 V
[In] Rated Current	13 A
Socket Number	4
Colour Tint	Green/black

Complementary

•	5
Outlet Standard	French
Cable Length	20 m
Cable Cross Section	1.5 mm ²
Type Of Cable	H05VV-F3G1.5
Height	260 mm
Width	352 mm
Depth	192 mm
Net Weight	4.43 kg

Environment

Ip Degree Of Protection

IP20

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	26.000 cm
Package 1 Width	29.500 cm
Package 1 Length	37.500 cm
Package 1 Weight	5.749 kg
Unit Type Of Package 2	P12

Number Of Units In Package 2	12
Package 2 Height	52.500 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	80.988 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information