Product datasheet

Specifications

, Green Premium[™]



Switch, Vivace, 16AX, 250V, 1 way, 1 gang, white

KB31_1_WE_G3

Main

Range	Vivace
Product Or Component Type	Switch
Device Short Name	KB31
Device Application	Control switch
Additional Switch Application	On/off switching
Number Of Rocker	1
Switch Function	1-way
Colour Tint	White

Complementary

Technology Type	Electromechanical
Device Presentation	Complete product
Actuator	Rocker
Number Of Gangs	1 gang
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Surface Finish	Glossy
Surface Treatment	Untreated
[Ue] Rated Operational Voltage	220250 V
Type Of Packing	Plastic bag
Network Type	AC
Quantity Per Set	1
Sale Per Indivisible Quantity	1
Rated Current	16 AX
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Connections - Terminals	Screw terminal

Embedding Depth	25 mm
Number Of Terminals	2
Rated Current	16 AX at 250 V AC, inductive 16 AX at 250 V AC, fluorescent 16 A at 250 V AC, resistive
[Ue] Rated Operational Voltage	250 V AC
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	2 screw terminals
Terminal Identifier	COM L1 L2
Tightening Torque	0.4 N.m
Clamping Connection Capacity	<= 2.5 mm² for rigid or stranded cable(s)
Wire Stripping Length	12 mm
Width	86 mm
Height	86 mm
Depth	37 mm

Environment

Standards	MS IEC 60669-1 IEC 60669-1 SS 227
Product Certifications	SNI
Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Operating Altitude	02000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

Number Of Units In Package 11Package 1 Height3.8 cmPackage 1 Width8.6 cmPackage 1 Length8.6 cmPackage 1 Weight63.0 gUnit Type Of Package 2BB1Number Of Units In Package 28Package 2 Height9.5 cmPackage 2 Width15.0 cmPackage 2 Length19.0 cmPackage 2 Weight635.0 g	-	
Package 1 Height3.8 cmPackage 1 Width8.6 cmPackage 1 Length8.6 cmPackage 1 Weight63.0 gUnit Type Of Package 2BB1Number Of Units In Package 28Package 2 Height9.5 cmPackage 2 Width15.0 cmPackage 2 Length19.0 cmPackage 2 Weight635.0 g	Unit Type Of Package 1	PCE
Package 1 Width8.6 cmPackage 1 Length8.6 cmPackage 1 Weight63.0 gUnit Type Of Package 2BB1Number Of Units In Package 28Package 2 Height9.5 cmPackage 2 Width15.0 cmPackage 2 Length19.0 cmPackage 2 Weight635.0 g	Number Of Units In Package 1	1
Package 1 Length8.6 cmPackage 1 Weight63.0 gUnit Type Of Package 2BB1Number Of Units In Package 28Package 2 Height9.5 cmPackage 2 Width15.0 cmPackage 2 Length19.0 cmPackage 2 Weight635.0 g	Package 1 Height	3.8 cm
Package 1 Weight63.0 gUnit Type Of Package 2BB1Number Of Units In Package 28Package 2 Height9.5 cmPackage 2 Width15.0 cmPackage 2 Length19.0 cmPackage 2 Weight635.0 g	Package 1 Width	8.6 cm
Unit Type Of Package 2 BB1 Number Of Units In Package 2 8 Package 2 Height 9.5 cm Package 2 Width 15.0 cm Package 2 Length 19.0 cm Package 2 Weight 635.0 g	Package 1 Length	8.6 cm
Number Of Units In Package 2 8 Package 2 Height 9.5 cm Package 2 Width 15.0 cm Package 2 Length 19.0 cm Package 2 Weight 635.0 g	Package 1 Weight	63.0 g
Package 2 Height9.5 cmPackage 2 Width15.0 cmPackage 2 Length19.0 cmPackage 2 Weight635.0 g	Unit Type Of Package 2	BB1
Package 2 Width 15.0 cm Package 2 Length 19.0 cm Package 2 Weight 635.0 g	Number Of Units In Package 2	8
Package 2 Length 19.0 cm Package 2 Weight 635.0 g	Package 2 Height	9.5 cm
Package 2 Weight 635.0 g	Package 2 Width	15.0 cm
	Package 2 Length	19.0 cm
Unit Type Of Package 3 CAR	Package 2 Weight	635.0 g
	Unit Type Of Package 3	CAR

Number Of Units In Package 3	80
Package 3 Height	21.0 cm
Package 3 Width	32.5 cm
Package 3 Length	50.0 cm
Package 3 Weight	6350.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations