Product datasheet





circuit breaker EasyPact Vigi CVS100B, 25 kA at 415 VAC, 50 A rating TM-D trip unit, MH Vigi module, 4P 3d

LV510374

! Discontinued on: Jan 23, 2021

! Discontinued

Main

Range	EasyPact
Product Name	EasyPact CVS
Device Short Name	Vigi CVS100B
Product Or Component Type	Earth leakage circuit breaker
Device Application	Distribution
Poles Description	4P
Protected Poles Description	3D
Earth Leakage Protection (Vigi Add On)	With
[In] Rated Current	50 A at 40 °C
Network Type	AC
Utilisation Category	Category A
[Icu] Breaking Capacity	40 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 25 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 20 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	50 A at 40 °C
Protection Type	Short-circuit protection (magnetic) Overload protection (thermal) Earth-leakage protection

Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to EN/IEC 60947-2
Network Frequency	50/60 Hz
Breaking Capacity Code	В
[Ics] Rated Service Breaking Capacity	15 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 25 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Neutral Position	Left
Mechanical Durability	30000 cycles
Electrical Durability	12000 cycles 415 V In conforming to IEC 60947-2
Control Type	Toggle

Thermal Protection Adjustment Range	3550 A
Neutral Protection Setting	No protection (3D)
Long Time Pick-Up Adjustment Type Ir	Adjustable
Long Time Pick-Up Adjustment Range	0.71 x ln
Long Time Delay Adjustment Type	Fixed
Instantaneous Pick-Up Adjustment Type Ii	Fixed
Instantaneous Pick-Up Adjustment Range	500 A
Earth-Leakage Add-On Module Name	MH
Earth-Leakage Protection Class	Class A
Residual Earth-Leakage Sensitity Adjustment Type	Adjustable 5 settings
[lõn] Residual Earth-Leakage Sensitive Adjustment	0.3 A
Sensitive Adjustment	1 A 3 A
	10 A
	30 A
Residual Earth-Leakage Time Delay Adjustment Type	Adjustable 5 settings
[Δt] Residual Earth-Leakage Time	0 ms 40 ms
Delay Adjustment	60 ms 140 ms
	150 ms 300 ms 310 ms 800 ms
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connections - Terminals	Screw connection
Connection Pitch	35 mm
Compatibility Code	CVS100
Width	140 mm
Depth	86 mm
Height	236 mm
Net Weight	2.2 kg
Environment	
Standards	EN 60947-2 IEC 60947-2
Product Certifications	GOST IEC
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40
Ambient Air Temperature For	-2570 °C
Operation	

-50...85 °C

Ambient Air Temperature For Storage

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free




Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


Dimensions Drawings





Туре	Α	A1	A2	A3	A4	A5	A6	A7	A8	A9	В	B1	B2	C1	C2	C3	E1
CV8106160/250	66.5	161	64	146	179.5	155.5	236	169	226	250.5	52.5	105	146	81	06	191@	62.5
C245/400/930	127.5	296	142.原	200	297	227.6	3.55	242.5	3.00	337	70	140	188	95.5	110	168	100
Type	E2	E3	E4	E5	E 6	E7	EB	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CWENTOWNSOUZEX	125	FE	140	137.5	200	145	215	216	17.5	70	86	78	13.5	25	17.5	24	y 32
CV5401431	200	113.5	2028	200	300	2125	327	45	22.5	90	-	-	-	-	-	32	y 35


(2) CJ-126mm for EasyPast CVS250B/F.

Assembly










Туре	Α	A1	A2	A3	A4	A/5	A6	A7	A8	A9	В	B1	B2	C1	C2	C3	E1
CV8100160/250	66.5	161	64	146	179.5	155.5	236	169	226	250.5	52.5	105	140	81	66	191@	62.5
C245/4000930	127.5	200	142,5	200	297	227.5	3.55	242.5	3.00	337	700	140	188	95.5	110	168	100
Type	E2	E3	E4	E5	E6	E7	E8	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CW9100M90/250	125	FE	140	137.5	200	145	215	216	17.5	70	55	78	13.5	23	17.5	24	y 32
CV5400/830	200	113.5	227	200	300	2135	327	45	22.5	90	-	000	-	-	-	32	y 35

(2) C3=126mm for EasyPast CVS2500/F.

Performance Curves



Reflex tripping.