Product datasheet

Specification





Enclosure, Resi9 MP, surface mounting, 1 row of 8 modules, IP40, white door, no terminal block

MIP10108

Main

| Range | Resi9 | |
|-----------------------------|-------------------|--|
| Product Name | Resi9 MP | |
| Product Or Component Type | Enclosure | |
| Enclosure Type | Modular enclosure | |
| Nb Of 18 Mm Modules Per Row | 8 | |
| Nb Of Horizontal Rows | 1 | |
| Type Of Door | Plain | |
| Width | 196 mm outside: | |
| Height | 198 mm outside: | |
| Depth | 95.5 mm outside: | |

Complementary

| Enclosure Mounting | Surface |
|-------------------------------|--|
| 9 Mm Pitches | 16 |
| Total Number Of 18 Mm Modules | 8 |
| [In] Rated Current | 63 A |
| Type Of Rail | 35 mm asymmetrical rail |
| Mounting Plate Description | Without mounting plate |
| Cable Entry | 1 bare flange 1 trunking flange |
| Terminal Block Function | Without |
| Enclosure Material | Back part: technoplastic Door: technoplastic Front face: technoplastic |
| Internal Depth | 80 mm |
| Colour | Door: white (RAL 9003) Front face: white (RAL 9003) |
| Market Segment | Residential |

Environment

| Quality Labels | IEC 60670-1 IEC 60670-24 | |
|----------------|-----------------------------|--|
| Standards | IEC 61439-1 IEC 61439-3 | |

| Fire Resistance | Door: 650 °C Back part: 650 °C Front face: 650 °C |
|--|---|
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK07 |
| Ambient Air Temperature For Operation | -2560 °C |

Packing Units

| . acimig cimes | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 10.2 cm |
| Package 1 Width | 19.6 cm |
| Package 1 Length | 22.8 cm |
| Package 1 Weight | 520.0 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 52.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 5.3 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 160 |
| Package 3 Height | 120.0 cm |
| Package 3 Width | 80.0 cm |
| Package 3 Length | 120.0 cm |
| Package 3 Weight | 96.8 kg |
| | |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free | |
|----------|----------------------------|-----|
| ⊘ | Rohs Exemption Information | Yes |
| ② | Halogen Free Product | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |