# **Product datasheet**

Specifications





Enclosure, Resi9 MP, surface mounting, 1 row of 8 modules, IP40, translucid door, no terminal block

MIP10108T

### Main

Range	Resi9
Product Name	Resi9 MP
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	8
Nb Of Horizontal Rows	1
Type Of Door	Translucid
Width	196 mm outside:
Height	198 mm outside:
Depth	101.5 mm outside:

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	16
Total Number Of 18 Mm Modules	8
[In] Rated Current	63 A
Type Of Rail	35 mm asymmetrical rail
Mounting Plate Description	Without mounting plate
Cable Entry	1 bare flange 1 trunking flange
Terminal Block Function	Without
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal Depth	80 mm
Colour	Front face: white (RAL 9003) Door: translucid
Market Segment	Residential

#### **Environment**

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24	
Quality Labels	IMQ	

Fire Resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-2560 °C

### **Packing Units**

r doming office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.200 cm
Package 1 Width	19.600 cm
Package 1 Length	22.800 cm
Package 1 Weight	520.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	52.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.300 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	96.800 kg
Package 3 Weight	96.800 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations