Product datasheet

Specifications

Sreen Premium™



Ulti - 250V 16 AX - 1 gang - 1 way - impress switch module - amber LED

U201SPM_1_A00_G3

() Discontinued on: Jan 23, 2021

① Discontinued

Main

Range	Ulti
Device Application	Control
Product Or Component Type	Switch module
Load Type	Fluorescent
Switch Application	Switch

Complementary

Bulb Type	LED amber
Rated Current	16 AX at 250 V AC 50 Hz
Number Of Cables	3 cable(s) 2.5 mm ²
Opening Distance	> 3 mm
Device Mounting	Flush
Fixing Mode	By screws
Distance Between Centers	60.3 mm
Number Of Gangs	1 gang
Switch Function	1-way
Width	87 mm
Height	87 mm
Depth	23.3 mm

Environment

Ambient Air Temperature For Operation	035 °C
Relative Humidity	095 %
Standards	BS EN 60669-1
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm

Package 1 Width	12.2 cm	
Package 1 Length	12.2 cm	
Package 1 Weight	64 g	

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations