

# Product datasheet

Specifications



## 20A 440V Weatherproof Surface Mount Double Pole Isolating Switch IP66

WHD20\_GY

! Discontinued on: 23 January 2021

! End-of-service on: 24 January 2021

! Discontinued - Service only

### Main

Range	Kavacha
Product or component type	Isolating switch
Device short name	W
Device application	Control

### Complementary

[Ie] rated operational current	20 A at 440 V AC-22A
Poles description	2P
Motor Rating	M180
Width	82 mm
Height	170 mm
Depth	90 mm

### Environment

IP degree of protection	IP66
Standards	IEC 60947-3
Environmental characteristic	Weatherproof

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	9 cm
Package 1 Length	8.3 cm
Package 1 Weight	733.333 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	36.5 cm
Package 2 Width	28.5 cm

Package 2 Length	43.5 cm
Package 2 Weight	22000 g
Unit Type of Package 3	P12
Number of Units in Package 3	540
Package 3 Height	130 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	414000 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)