Product datasheet

Specifications





Complete miniature beacon, Harmony XVDLS Optimum, 45mm, tower light, steady, red, IP40, 250V

XVDLS34

① Discontinued

(!) Discontinued on: Sep 30, 2023

Main

Range Of Product	Harmony XVD Optimum
Product Or Component Type	Complete miniature beacon
Beacon Or Indicator Bank Unit Type	Base unit direct fixing Illuminated unit
Signalling Type	Steady
Mounting Diameter	45 mm
Component Name	XVDLS
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Bulb not included, red
Bulb Type	Incandescent with BA 15d base
[Us] Rated Supply Voltage	<= 230 V
Maximum Bower Dissinction In W	E MI

Maximum Power Dissipation In W 5 W

Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end
Cable Entry	1 entry tapped for Pg 7
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Cad Overall Width	45 mm
Cad Overall Height	104 mm
Cad Overall Depth	45 mm
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW
Net Weight	0.08 kg

Environment

Product Certifications	UL CSA
Standards	EN/IEC 60947-5-1
Protective Treatment	тс
Ambient Air Temperature For Operation	-2570 °C

Ambient Air Temperature For Storage	-4070 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ip Degree Of Protection	IP40 conforming to IEC 60529

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	5.6 cm
Package 1 Length	5.6 cm
Package 1 Weight	101 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	12
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.405 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards


Circularity Profile	No need of specific recycling operations
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

Product datasheet

Dimensions Drawings

Illuminated Beacon

Dimensions



Product datasheet

Mounting and Clearance

Illuminated Beacon

Panel Cut-out for Direct Fixing

